

EC Declaration of Conformity

Manufacturer: **Neobiotech Co., Ltd.**

#104/24, #102, 103, 104-1, 104-2, 105, 106, 205, 212,312,509,510,511 / 10F, 36,
Digital-ro27Gil, Guro-gu, Seoul, 08381, Korea

European representative: DongBang Acuprime(EU), Inc.

1 Forrest Units, Hennock Road East, Marsh Barton, Exeter EX2 8RU, U.K
Tel : +44 1392 829500 Fax: +44 1392 823232

Product

Dental Surgical Instruments: SLA Kit, SCA Kit, Neo FR Kit, Neo SR Kit

All In One Kit, IS Core Kit, S-Wide Kit,

Neo punch Kit, S-Mini kit, IS Kit, GBR Kit, EZ-GBR Kit

IS Full Kit, EB&IT Kit, Accessory Kit, Prosthetic Kit,

Universal Prosthetic Kit, IS Pick Cap Impression Kit,

Guide Kit, NAVI Guide Kit

Stop Drill Kit, Prosthetic Planning Kit, Neo Sinus All Kit

Ridge Wider Kit , Neo Surgical Kit

Other Surgical Components

Classification: Class IIa by Rule 6 of Annex IX, MDD 93/42/EEC as amended by 2007/47/EC

Conformity Assessment Route: Annex II, Excluding Section 4, MDD 93/42/EEC as amended
by 2007/47/EC

We hereby declare that complies with the Medical Devices Directive 93/42/EEC as amended by 2007/47/EC (and its relevant transposition into the national laws of the Member States in which the device is intended to be placed on the market) using Annex II as the conformity assessment procedure via SGS(NB 0120) as the Notified Body.


Applied standards;

- EN ISO 14971:2012 Medical devices – Application of risk management to medical devices
- ISO 13485:2003 Medical devices – Quality management system – Requirements for regulatory Purposes
- EN:1639:2010 Dentistry. Medical devices for dentistry. Instruments
- ISO 11137-1:2006 Sterilization of health care products -- Radiation -- Part 1: Requirements for development, validation and routine control of a sterilization process for medical devices

Notified Body: SGS United Kingdom International Certification Services Limited
Unit 202B, Worle Parkway Weston-Super-Mare North Somerset
BS 22 OWA United Kingdom

Place, Date of issue: #104/24, #102, 103, 104-1, 104-2, 105, 106, 205, 212,312,509,510,511 / 10F, 36,
Digital-ro27Gil, Guro-gu, Seoul, 08381, Korea
on Jan 19th, 2017

Signature :



President on behalf of
Neobiotech Co., Ltd

- Product Schedule Attached

Product Schedule

TCF02(Rev.12)

SLA Kit (SLAKIT)

- C-Reamer** : SLC40, SLC50, SLC60, SLC415, SLC430, SLC515, SLC530, SLC615, SLC630, LC520, LC535, LC620, LC635, LC720, LC735, SLC515L, SLC530L, SLC615L, SLC630L
- LS Reamer** : SLS40, SLS50, SLS60, SLS420, SLS435, SLS520, SLS535, SLS620, SLS635, SLS420L, SLS435L, SLS520L, SLS535L, SLS620L, SLS635L, LS520, LS535, LS620, LS635, LS720, LS735
- Sinus Elevator** : SLE01, SLE02, SLE03, SLE04, SLE05
- C-Guide** : SCG510L, SCG610L, SCG510, SCG610, SCG710
- SLA Tray** : SLAKIT

SCA Kit (SCAKIT)

- **S-reamer** : ICR24, ICR28, ICR32, ICR36
- Initial Drill** : SSD20
- Depth Gauge** : SDG00
- Stopper** : SKS01, SKS02, SKS03, SKS04, SKS05, SKS06, SKS07, SKS08, SKS09, SKS10, SKS11, SKS12
- Bone condenser** : SBC01, SBC02
- Bone Spreader** : SBS20, SBS30
- Bone Insertter** : SBI 27
- Bone Carrier** : JUMBO, JUMBO2
- SCA Stopper Holder** : SSH
- SCA Tray** : SCAKIT

Neo FR Kit (FRKIT)

- FR Screw Hex driver** : HDF1607, HDF1612, HDF1617
- Fixture Remover** : FR310, FR315, FR320, FR410, FR415, FR420, FR510, FR515, FR520, FR610, FR615, FR620, FR710, FR715, FR720
- Fixture Remover Screw** : EFRS16, EFRS20, EFRS25, IFRS18, IFRS20, FRS14, FRS16, FRS172, FRS18, FRS20, FRS25, FRS154
- Torque Wrench** : TW300, TW400, TW500, TW80400
- Ratchet** : ITRCHT, FRCHT
- FR Kit Tray** : FRKIT

Neo SR Kit (SRKIT)

- Reverse Drill** : RCD08, RCD10, RCD12, RCD14
- Claw** : CD16, CD18, CD20, CD25
- PG Hand Driver** : PGHD25S, PGHD25, PGHD25SS, PGHD25SP
- Screw Remover** : SR08, SR10, SR12, SR14
- Shank driver** : SHD00
- Perfect Guide** : PG0816, PG1018, PG1220, PG1425
- Conical Guide** : CG00

- Internal Guide** : IHG24, IHG25, IOG31
- External Guide** : EHG24, EHG27, EHG34
- Guide Holder** : GH00
- SR Driver Holder** : SRDH01
- SR Kit Tray/SR Kit2 Tray** : SRKIT / SRKIT2

All In One Kit (AIOKIT)

- Guide Drill** : GD20
- Surgical Drill** : TSD20, TSD29, TSD33, TSD35, TSD38, TSD41, TSD43, TSD48, TSD50, TSD55, TSD60, TSD65, TSD70, TSD75 TSD20S, TSD29S, TSD33S, TSD35S, TSD38S, TSD41S, TSD43S, TSD48S, TSD50S, TSD55S, TSD60S, TSD65S, TSD70S, TSD75S
TSD20L, TSD29L, TSD33L, TSD35L, TSD38L, TSD41L, TSD43L ,TSD48L, TSD50L, TSD55L, TSD60L, TSD65L, TSD70L, TSD75L ,TSD45
TSD45S, TSD45, CSD2007, CSD2008, CSD2010, CSD2011, CSD2013, CSD2015, CSD2907, CSD2908, CSD2910, CSD2911, CSD2913, CSD2915, CSD3307, CSD3308, CSD3310 ,CSD3311, CSD3313 , CSD3315, CSD3507, CSD3508, CSD3510, CSD3511, CSD3513, CSD3515, CSD3807, CSD3808, CSD3810, CSD3811, CSD3813L, CSD3815, CSD4107, CSD4108,, CSD4110, CSD4111, CSD4113, CSD4115, CSD4307, CSD4308, CSD4310 ,CSD4311, CSD4313, CSD4315, CSD4807, CSD4808, CSD4810, CSD4811, CSD4813, CSD4815, CSD5007, CSD5008, CSD5010, CSD5011, CSD5013, CSD5015, CSD5507, CSD5508, CSD5510, CSD5511, CSD5513, CSD5515, CSD6007, CSD6008, CSD6010, CSD6011, CSD6013, CSD6015, CSD6507, CSD6508, CSD6510, CSD6511, CSD6513, CSD6515, CSD7007, CSD7008, CSD7010, CSD7011, CSD7013 , CSD7015, CSD7507 , CSD7508, CSD7510, CSD7511, ,CSD7513, CSD7515
- EB/IT Multi Profile** : MP 00, MP 55, MP 60, MP 70, MP 80
- IS Multi Profile** : ISCS 35, ISCS 40, ISCS 45, ISCS 50
- Tap Drill** : ISTD 35, ISTD 40, ISTD 45, ISTD 50, BISTD 50, TD 55, TD 60, TD 70
- **Adapter** : CAA 00, RC 05, RC 10, RC 15, RC 20, RC 25
- Direction Pin** : DPE40, DPE50, DPE60, DPI40, DPI50, DPI60
- Stopper** : DS030, DS040, DS050, DS060, DS063, DS070, DS085, DS100, DS115, DS130, DS070S, DS085S, DS100S, DSL060, DSL070, DSL085, DSL100, DSL115
- Drill Extension** : DE01
- Fixture Driver** : EBFDH24, EBFDH27, EBFDH34, ITFDO 31, ISFDH 25, ISFDH25S, ISFDH 25L, ISFDH 25EL
- Hex Driver** : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S
HDC0910, HDC0915, HDC1205, HDC1207, HDC1210, HDC1212, HDC1215, HDC1220
- Parallel Pin** : PP 08, PP 10, PP 11
- Depth Gauge**: MG00
- Torque Ratchet** : TW01
- Tissue Punch** : TP45, TP55, TP65
- AIO Kit Tray** : AIOKIT

IS Core Kit (ISCKIT)

- Guide Drill** : GD20
- Surgical Drill** : TSD20, TSD29, TSD33, TSD35, TSD38, TSD41, TSD43, TSD45
- IS Multi Profile** : ISCS 35, ISCS 40, ISCS 45, ISCS 50
- Tap Drill** : ISTD 35, ISTD 40, ISTD 45, ISTD 50, BISTD 50,
- **Adapter** : CAA 00, RC 15
- Stopper** : DS070, DS085, DS100, DS115, DS130,
- Fixture Driver** : ISFDH25
- Hex Driver** : HD1215
- Torque Ratchet** : TW01
- IS Core Kit Tray** : ISCKIT

Neo Punch Kit (TBTP01SET)

- Tissue Punch** : TP35, TP40, TP45, TP50, TP55, TP60, TP65, TP70
- Trephine Drill** : TB40, TB50, TB60, TB70, TB80

S-Wide Kit (SWKIT)

- S-Wide Surgical Drill** : TSD48, TSD50, TSD55, TSD60, TSD65
- S-Wide Multi Profile** : MP55, MP60, MP70
- Connector**: CAA00, RC15
- S-Wide Tap Drill** : TD55, TD60, TD70
- S-Wide Drill Stopper** : DSL060, DSL070, DS085, DS100, DS115
- Hex Driver** : HD1212
- Trephine Drill**: TB40, TB50
- Stopper Holder** : DSHL
- S-Wide Kit Tray** : SWKIT

S-mini Kit (SMKIT)

- S-mini Guide Drill** : MGD12
- S-mini Surgical Drill** : MSD15, MSD20, MSD25, MSD30
- S-mini Tap Drill** : MTD25, MTD30, MTD35
- Mini Implant Fixture Driver** : ISQD20, BADH24, BADH24R
- Connector**: CAA00
- Ratchet Connector** : RC10, RC15
- S-mini Parallel Pin** : MPP08, MPP10, MPP11
- S-mini Kit Tray** : SMKIT

GBR Kit(GBRKIT)

- Screw Fixation Drill**: SFD05, SFD06, SFD07, SFD08, SFD09, SFD10, SFD11, SFD12, SFD13, SFD14 , SFD15, SFD16, SFD17, SFD18, SFD19, SFD20, SFD21, SFD22, SFD23, SFD24, SFD25
- Dual Hex Driver** : DHDH15, DHDH15S, DHDR10, DHDR15, DHDR20, DHDR10S, DHDR15S, DHDR20S, DHDC10, DHDC20
- Hex Driver** : HDH0910, HDH0915, HDH1205, HDH1207, HDH1210, HDH1212, HDH1215, HDH1220 ,HDH1225,

HDH1230, HDH1235, HDH1240, HDH1250, HDH12505, HDH12507, HDH12510, HDH12512, HDH12515, HDH12520, HDH12525, HDH12530, HDH12535, HDH12540 ,HDH12550, HDH0910S, HDH0915S, HDH1205S, HDH1207S, HDH1210S, HDH1212S, HDH1215S, HDH1220S, HDH1225S, HDH1230S, HDH1235S0, HDH1240S, HDH1250S, HDH12505S, HDH12507S, HDH12510S, HDH12512S, HDH12515S, HDH12520S, HDH12525S, HDH12530S, HDH12535S, HDH12540S, HDH12550S

-Philips Head Screw Driver : PHSD05, PHSD10, PHSD20, PHSD30, PHSD40

-Driver Handle: DRH

-Screw Fixation Drill Stopper : SFDS010, SFDS020, SFDS030, SFDS040, SFDS050, SFDS060, SFDS070, SFDS080, SFDS090

-Screw Fixation Drill Stopper Holder : SFDSH

-GBR Kit Ratchet Connector : GRC05, GRC10, GRC15

-GBR Kit Tray : GBRKIT

EZ-GBR Kit(EZGBRKIT)

-Screw Fixation Drill: SFD05, SFD06, SFD07, SFD08, SFD09, SFD10, SFD11, SFD12, SFD13, SFD14 , SFD15, SFD16, SFD17, SFD18, SFD19, SFD20, SFD21, SFD22, SFD23, SFD24, SFD25

-EZ-Screw Fixation Drill : EZSFD17

-Dual Hex Driver : DHDH15, DHDH15S, DHDR10, DHDR15, DHDR20, DHDR10S, DHDR15S, DHDR20S, DHDC10, DHDC20

-Philips Head Screw Driver : PHSD05, PHSD10, PHSD20, PHSD30, PHSD40

-EZ -Philips Head Screw Driver : EZPHD3502, EZPHD3512, EZPHD3520

- EZ-Break Driver: EZBRD

- EZ-Cover Cap Driver: EZCCD42

- EZ-Handle Connector: EZHC12

- EZ-Ti-Mem Push Driver: EZPD68

- EZ-Screw Fixation Drill Stopper : EZSFDS050

-EZ-GBR Kit Tray : EZGBRKTC, EZGBRKITT

IS Full Kit (ISFKIT, ISFFKIT)

-Lindemann Drill : LDS25, LDS23 ,LDS23C

-Surgical Drill : TSD22F, TSD22FS, TSD29FS, TSD34FS, TSD39FS, TSD44FS, TSD29F, TSD34F, TSD39F, TSD44F, TSD49F , TSD22CS, TSD22CL, TSD30CS, TSD30CL, TSD35CS, TSD35CL, TSD40CS, TSD40CL, TSD45CS, TSD45CL

-Profile Tap: PTAP35F, PTAP40F, PTAP45F, PTAP50F, PTAP55F, PTAP35FS, PTAP40FS, PTAP45FS, PTAP50FS, PTAP55FS,

- IS Cortical Drill : ISCD35F, ISCD40F, ISCD45F, ISCD50F

-Multi Profile : ISCS35F, ISCS40F, ISCS45F, ISCS50F, ISCS55F

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

-Stopper : DS030F, DS040F, DS050F, DS060F, DS070F, DS085F, DS100F, DS115F, DS130F, DS030C, DS040C, DS050C, DS060C, DS066C, DS070C, DS085C, DS100C, DS115C, DS130C

-Stopper Holder : DSHF, DSHC

-IS Fixture Driver : ISFDH02F, ISFDH05F, ISFDH07F, ISFDH10F, ISFDH12F, ISFDH15F, ISFDH17F, ISFDH20F , ISFDH22F, ISFDH25F, ISFDH27F, ISFDH30F, ISFDH32F, ISFDH35F, ISFD05C, ISFD05CL, ISFDR05F, ISFDR07F, ISFDR10, ISFDR10F, ISFDR12F, ISFDR15, ISFDR15F, ISFDR17F, ISFDR20F, ISFDR22F, ISFDR25F, ISFDR27F, ISFDR30F, ISFDR32F, ISFDR35F, ISFDR37F, ISFD10R, ISFD15R

-Parallel Pin : PP07F, PP08F, PP10F, PP11F

-Direction Pin : DPI40, DPI 50, DPI 60, DPIS50, DPIS60, DPIS35C , DPIS45C

-Drill Extension : DE01

-Ratchet Connector : RC05, RC10, RC15, RC20, RC25, CAA00

-Depth Gauge : MG00, DG17

-Torque Ratchet : TW01, TW60

-Driver Holder : DH01, DH02

-Profile Tap Support Holder : SGPTSH

-IS Full Kit Tray : ISFKIT, ISFFKIT

EB&IT Kit (EBITKIT)

-Surgical Drill : TSD22F, TSD22FS, TSD29FS, TSD34FS, TSD39FS, TSD44FS, TSD29F, TSD34F, TSD39F, TSD44F, TSD49F

-Lindemann Drill : LDS25, LDS23

-Multi Profile : MP00

-Tap Drill : ISTD35, ISTD40, ISTD45, ISTD50

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

-Stopper : DS030F, DS040F, DS050F, DS060F, DS070F, DS085F, DS100F, DS115F, DS130F

-Stopper Holder : DSHF

-Fixture Driver : EBFDH24, EBFDH27, EBFDH34, ITFDO31

-Drill Extension : DE01

-Fixture Direction Pin : DPE40, DPE50, DPE60, DPI50, DPI60

-Parallel Pin : PP07F, PP08F, PP10F, PP11F

-Ratchet Connector : RC05, RC10, RC15, RC20, RC25, CAA00

-Depth Gauge : MG00, DG17

-Torque Ratchet : TW01, TW60

-EB&IT Kit Tray : EBITKIT

Accessory Kit(ACCKIT)

-Bone Planer : BP35, BP40, BP45, BP50, BP55, BP60, BP65, BP70, BP75, BP80

-Dia Marker : DM35, DM40, DM45, DM50, DM55, DM60, DM65, DM70, DM75, DM80

-Bone Profile : BPN40, BPR50, BPR60, BPB60, BPI60, BPB70, BPB80, BPB90, ISBP48, ISBP55, ISBP60, ISBP68

-Quick Tight : QTH1205, QTH1210, QTH1215, QTH1220, QTH1225, QTH1230, QTH12505, QTH12510, QTH12515, QTH12520

QTH12525, QTH12530, QTH12535

-Tissue Punch : TP35, TP40, TP45, TP50, TP55, TP60, TP65, TP70

-Ratchet Connector : RC05, RC10, RC15, RC20, RC25

-Accessory Kit Tray : ACCKIT

Prosthetic Kit (PRTKIT, UVPRTKIT)

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S, HDC0910, HDC0915, HDC1205, HDC1207, HDC1210, HDC1212, HDC1215, HDC1220, HDC12505, HDC12510, HDC12515, HDC12520, HDC12525, HDC12530, HDC12535, : HDH0910, HDH0915, HDH1205, HDH1207, HDH1210, HDH1212, HDH1215, HDH1220 ,HDH1225, HDH1230, HDH1235, HDH1240, HDH1250, HDH12505, HDH12507, HDH12510, HDH12512, HDH12515, HDH12520, HDH12525, HDH12530, HDH12535, HDH12540 ,HDH12550, HDH0910S, HDH0915S, HDH1205S, HDH1207S, HDH1210S, HDH1212S, HDH1215S, HDH1220S, HDH1225S, HDH1230S, HDH1235S, HDH1240S, HDH1250S, HDH12505S, HDH12507S, HDH12510S, HDH12512S, HDH12515S, HDH12520S, HDH12525S, HDH12530S, HDH12535S, HDH12540S, HDH12550S

-Rescue Hex Driver : HD1205RC, HD1210RC, HD1212RC, HD1215RC, HD1220RC, HD1225RC, HD1230RC, HD1235RC, HD12505RC, HD12510RC, HD12512RC, HD12515RC, HD12520RC, HD12525RC, HD12530RC, HD12535RC, HD1205RCS, HD1210RCS, HD1212RCS, HD1215RCS, HD1220RCS, HD1225RCS, HD1230RCS, HD1235RCS, HD12505RCS, HD12510RCS, HD12512RCS, HD12515RCS, HD12520RCS, HD12525RCS, HD12530RCS, HD12535RCS

-Angled Driver: HDA1215, HDA1220, HDA1225, HDA12515, HDA12520, HDA12525, HDA1215S, HDA1220S, HDA1225S, HDA12515S, HDA12520S, HDA12525S

-Abutment Positioner : AP162N, AP165N, AP167N, AP202N ,AP205N , AP207N, AP252N , AP255N, AP257N

-Abutment Positioner set : AP1612SET, AP2012SET, AP2512SET, AP16125SET, AP20125SET, AP25125SET, APSET

-Torque Ratchet : TW01, TW60

-Abutment Positioner Holder : APH

-SCS Driver : SCSD10S , SCSD15S

-Unigrip Driver : UGD10S, UGD15S

-Driver Holder : DH02

-Prosthetic Kit Tray : PRTKIT, UVPRTKIT

Pick Cap Impression Kit (PCIKIT)

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230,

HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

-Abutment Positioner : AP162N, AP165N, AP167N, AP202N ,AP205N , AP207N, AP252N , AP255N, AP257N

-IS Pick Cap Impression Body : ISPCIB3503, ISPCIB3505, ISPCIB3508, ISPCIB3510, ISPCIB4003, ISPCIB4005, ISPCIB4008, ISPCIB4010, ISPCIB403 ,ISPCIB405, ISPCIB408, ISPCIB410, ISPCIB502, ISPCIB503, ISPCIB504, ISPCIB505, ISPCIB506, ISPCIB602, ISPCIB603, ISPCIB604, ISPCIB605, ISPCIB606, ISPCIB702, ISPCIB703 ,ISPCIB704, ISPCIB705, ISPCIB706, ISPCIB803, ISPCIB804, ISPCIB903, ISPCIB904

- EB Pick Cap Impression Body : EBPCIBN403, EBPCIBN405, EBPCIBR403, EBPCIBR405, EBPCIBR503, EBPCIBR505, EBPCIB603, EBPCIB605, EBBPCIB603, EBBPCIB605

- IT Pick Cap Impression Body : ITPCIB503, ITPCIB703

-Pick Cap Impression Cap : PCISC01, PCILC01

-IS Pick Cap Impression Screw : ISPCIS20

-EB Pick Cap Impression Screw : EBPCIS16, EBPCIS20, EBPCIS25

-Pick Cap Impression Pincette : PCIPC

-Pick Cap Impression Set : ISPCIB3503C, ISPCIB3505C, ISPCIB3508C, ISPCIB3510C, ISPCIB4003C, ISPCIB4005C, ISPCIB4008C ISPCIB4010C, ISPCIB403C, ISPCIB405C, ISPCIB408C, ISPCIB410C, ISPCIB502C, ISPCIB503C, ISPCIB504C, ISPCIB505C, ISPCIB506C, ISPCIB602C, ISPCIB603C, ISPCIB604C, ISPCIB605C, ISPCIB606C, ISPCIB702C, ISPCIB703C, ISPCIB704C, ISPCIB705C, ISPCIB706C, ISPCIB803C, ISPCIB804C, ISPCIB903C, ISPCIB904C, ISPCIB3503S, ISPCIB3505S, ISPCIB3508S, ISPCIB3510S, ISPCIB4003S, ISPCIB4005S , ISPCIB4008S , ISPCIB4010S , ISPCIB403S, ISPCIB405S, ISPCIB408S, ISPCIB410S, ISPCIB502S, ISPCIB503S, ISPCIB504S, ISPCIB505S, ISPCIB506S, ISPCIB602S, ISPCIB603S, ISPCIB604S, ISPCIB605S, ISPCIB606S, ISPCIB702S, ISPCIB703S, ISPCIB704S, ISPCIB705S, ISPCIB706S, ISPCIB803S, ISPCIB804S, ISPCIB903S, ISPCIB904S, PCISC01, PCISC01, PCILC01, PCILC01

EBPCIBN403C, EBPCIBN405C, EBPCIBR403C, EBPCIBR405C, EBPCIBR503C, EBPCIBR505C, EBPCIB603C, EBPCIB605C, EBBPCIB603C, EBBPCIB605C, EBPCIBN403S, EBPCIBN405S, EBPCIBR403S, EBPCIBR405S, EBPCIBR503S, EBPCIBR505S, EBPCIB603S, EBPCIB605S, EBBPCIB603S, EBBPCIB605S

ITPCIB503C, ITPCIB703C, ITPCIB503S, ITPCIB703S

-Pick Cap Impression Kit Tray : PCIKITTRAY

-Pick Cap Impression Kit Tray Cover: PCIKITCOVER

Guide Kit(GUIDEKIT , NEONGKIT)

-Surgical Guide Drill : SGD22S, SGD22L, SGD29S, SGD29L, SGD34S, SGD34L, SGD39S, SGD39L, SGD44S, SGD44L, SGD1505, SGD1510, SGD1513, SGD2207, SGD2208, SGD2210, SGD2211, SGD2213, SGD2907, SGD2908, SGD2910, SGD2911, SGD2913

-Surgical Guide Counter sink : SGCS35N, SGCS40R, SGCS45R, SGCS50W

- Surgical Guide IS Fixture Profile Tap : SGISFPT35N, SGISFPT40R, SGISFPT45R, SGISFPT50W

- Surgical Guide Lateral Anchor Drill : SGLAD15L, SGLAD15S,

- Surgical Guide Bone Planer: SGBP2210, SGBPR2207

-Neo Guide Point Drill : NGPD24

- Neo Guide Taper Drill : NGTD2207, NGTD2208, NGTD2210, NGTD2211, NGTD2213, NGTD2214, NGTD 3007, NGTD3008, NGTD3010, NGTD3011, NGTD3013, NGTD3014, NGTD3507, NGTD3508, NGTD3510, NGTD3511, NGTD3513, NGTD3514, NGTD4007, NGTD4008, NGTD4010, NGTD4011, NGTD4013, NGTD4014, NGTD4507, NGTD4508, NGTD4510, NGTD4511, NGTD4513, NGTD4514

-Neo Guide Cortical Tap : NGISCT35N, NGISCT40R, NGISCT45R, NGISCT50W

-Neo Guide Cortical Drill : NGCD35F, NGCD40F, NGCD45F, NGCD50F

-Bone Profiler : ISBP48, ISBP55, ISBP60, ISBP68

-Neo Guide Bone Trimmer: NGBT00, NGBT15, NGBT30

-Neo Guide Twist Drill: NGTWD2207, NGTWD2208, NGTWD2210, NGTWD2211, NGTWD2213, NGTWD2214

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

- Surgical Guide Drill Stopper : SGDS020, SGDS030, SGDS040, SGDS050, SGDS060, SGDS070, SGDS073, SGDS085

- Surgical Handle Guide : SGHG22N,SGHG29N, SGHG22RW, SGHG29RW

- Surgical Guide IS Fixture Driver : SGISFDRN, SGISFDRRW, SGISFDHN, SGISFDHRW

-Neo Guide IS Fixture Driver : NGISFDR,NGISFDCA

- Surgical Guide Tissue Punch : SGTP38N, SGTP43R, SGTP50W

-Neo Guide Tissue Punch : NGTP38N, NGTP43R, NGTP50W

- Surgical Guide Sleeve : SGS55N, SGS70RW, SGS22SD

- Surgical Guide Lateral Anchor Sleeve : SGLAS30S, SGLAS30L

- Surgical Guide IS Vertical Anchor Body: SGISVABFN, SGISVABFRW, SGVABBN, SGVABBRW,

- Surgical Guide IS Vertical Anchor Screw : SGISVASF, SGVASB

- Surgical Guide IS Vertical Anchor Set : SGISVAFN, SGISVAFRW, SGVABN, SGVABRW

-NeoGuide IS Vertical Anchor Body: NGISVABFN, NGISVABFRW, NGVABBN, NGVABBRW

- NeoGuide IS Vertical Anchor Screw: NGISVAS, NGVASB

- NeoGuide IS Vertical Anchor set : NGISVAFN, NGISVAFRW, NGVABN, NGVABRW

-Surgical Guide IS Fixture Adapter Body : SGISFABN, SGISFABRW,SGISFABN30, SGISFABRW30

- Surgical Guide IS Fixture Adapter Screw : SGISFAS, SGISFAS30

- Surgical Guide IS Fixture Adapter set : SGISFABN, SGISFABRW, SGISFAN30, SGISFARW30

- Surgical Guide Lateral Anchor pin : SGLAP18L, SGLAP18S

- Surgical Guide Adapter Removal Tool ; SGFART0

- Surgical Guide Drill Stopper Holder : SGDSH22

-Profile Tap Support Holder : SGPTSH

-Guide Connector : SGCAC00, SGRC10, SGRC15

-Torque Ratchet : TW60

-Guide Kit Tray : GUIDEKIT , NEONGKIT

Stop Drill Kit(STOPDRILLKIT)

-Surgical Stop Drill : TSD2207, TSD2208, TSD2210, TSD2211, TSD2213, TSD2907, TSD2908, TSD2910, TSD2911, TSD2913, SD3407, TSD3408, TSD3410, TSD3411, TSD3413, TSD3907, TSD3908, TSD3910, TSD3911, TSD3913, TSD4407, TSD4408, TSD4410, TSD4411, TSD4413, TSD4907, TSD4908, TSD4910, TSD4911, TSD4913

-Profile Tap: PTAP35F, PTAP40F, PTAP45F, PTAP50F, PTAP55F, PTAP35FS, PTAP40FS, PTAP45FS, PTAP50FS, PTAP55FS

-Multi Profile : ISCS35F, ISCS40F, ISCS45F, ISCS50F, ISCS55F

-Lindemann Drill : LDS25, LDS23

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

-Drill Extension : DE01

-Ratchet Connector : RC05, RC10, RC15, RC20, RC25

-Fixture Driver : ISFDH02F, ISFDH05F, ISFDH07F, ISFDH10F, ISFDH12F, ISFDH15F, ISFDH17F, ISFDH20F , ISFDH22F, ISFDH25F, ISFDH27F, ISFDH30F, ISFDH32F, ISFDH35F, ISFD05C, ISFDR05F, ISFDR07F, ISFDR10, ISFDR10F, ISFDR12F, ISFDR15, ISFDR15F, ISFDR17F, ISFDR20F, ISFDR22F, ISFDR25F, ISFDR27F, ISFDR30F, ISFDR32F, ISFDR35F, ISFDR37F, ISFD10R, ISFD15R

-Parallel Pin : PP07F, PP08F, PP10F, PP11F

-Direction Pin : DPI40, DPI 50, DPI 60, DPIS50, DPIS60

-Profile Tap Support Holder: SGPTSH

-Torque Ratchet : TW60

-Depth Gauge : MG00, DG17

-Driver Holder : DH01, DH02

-Stop Drill Kit Tray : STOPDRILLKIT

Prosthetic Planning Kit(PRTPNKIT)

-Prosthetic Planning : PISAH415, PISAH425, PISAH435, PISAH445, PISAH515, PISAH525, PISAH535, PISAH545, PISAH615, PISAH625, PISAH635, PISAH645, PISAH715, PISAH725, PISAH735, PISAH745, PISAHA1427, PISAHA1447, PISAHB1427, PISAHB1447, PISAHA1527, PISAHA1547, PISAHB1527, PISAHB1547, PISAHA1627, PISAHA1647, PISAHB1627, PISAHB1647, PISAHA2427, PISAHA2447, PISAHB2427, PISAHB2447, PISAHA2527, PISAHA2547, PISAHB2527, PISAHB2547

-Prosthetic Planning Holder : PRTPNH, PRTPNSH

-Prosthetic Planning Kit Tray : PRTPNKIT

Neo SinusAll Kit(SAKIT)

-Initial Drill : SAD22

-Sinus All Drill : SAD28, SAD32, SAD37, SAD40

-S-Reamer : SASR28, SASR32, SASR36, SASR39

-C-Reamer : SAC640

-C-Guide : SACG610

-LS-Reamer : SALS640

-Hex Driver : HD0910, HD0915, HD1205, HD1207, HD1210 , HD1212, HD1215 , HD1220, HD1225, HD1230, HD1235, HD1240, HD1250, HDD12505 , HDD12510, HDD12515, HDD12520, HDD12525 ,HDD12530, HDD12540, HDD12550, HD12505, HD12510, HD12512, HD12515, HD12520, HD12525, HD12530, HD12535, HD12540, HD12550, HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S, HD12505S, HD12510S, HD12512S, HD12515S, HD12520S, HD12525S, HD12530S, HD12535S, HD12540S, HD12550S

-Rotary Elevator : SARE28, SARE32, SARE36, SARE39

-Sinus Elevator : SLE01, SLE02, SLE03

-Crestal Stopper : CDS010, CDS020, CDS030, CDS040, CDS050, CDS060, CDS070, CDS080, CDS090, CDS100, CDS110, CDS120

-Lateral Stopper : LTS010, LTS020, LTS030, LTS040

-Stopper Holder : DSHF, LTSH

-Side Cutter : SCT30

-Bone Carrier : JUMBO, JUMBO2

-Bone Condenser : SABCO1

-Aqua Tap : AQT

-Aqua system(Set) : AQST

-Aqua Valve : AQVV

-Aqua Hose : AQHS

-Aqua Syringe : AQSRG

-Aqua Syringe Connector : AQSRGC

-Drill Handle : SADH01

-Depth Gauge : SADG01

-Torque Ratchet : TW60

-Fixture Driver : ISFDH02F, ISFDH05F, ISFDH07F, ISFDH10F, ISFDH12F, ISFDH15F, ISFDH17F, ISFDH20F, ISFDH22F, ISFDH25F, ISFDH27F, ISFDH25SF, ISFDH25LF, ISFDH30F, ISFDH32F, ISFDH35F, ISFDR05F, ISFDR07F, ISFDR10, ISFDR10F, ISFDR12F, ISFDR15, ISFDR15F, ISFDR17F, ISFDR20F, ISFDR22F ,ISFDR25F, ISFDR27F, ISFDR30F, ISFDR32F, ISFDR35F, ISFDR37F

-Neo SinusAll Kit Tray : SAKIT

Ridge Wider Kit (RWKIT)

-S-mini Surgical Drill : MSD15, MSD20, MSD25, MSD30

-Bone Trimmer : BTRI6010

-Bone Expander : BEXP30, BEXP 35, BEXP 40, BEXP 45

-Saw Disk : SAWD07, SAWD10, SAWD13, SAWDT07, SAWDH10, SAWDH13

-Ridge Spreader Bone Chisel : BCHI60

-Ratchet Connector : RC05, RC10, RC15, RC20, RC25

-Torque Ratchet: TW60

-Ridge Wider Kit Tray : RWKIT

Neo Surgical Kit (NEOSKIT)

-Lindemann Drill : LDS23C

-Twist Surgical Drill : TSD22CS, TSD22CL, TSD30CS, TSD30CL, TSD35CS, TSD35CL, TSD40CS, TSD40CL, TSD45CS, TSD45CL

- IS Cortical Drill : ISCD35F, ISCD40F, ISCD45F, ISCD50F

- Profile Tap : ISTD38S ,ISTD43S, ISTD35S, ISTD40S, ISTD45S, ISTD50S, ISTD55S, ISTD60S, ISTD70S

- Hex Driver : HD0910S, HD0915S ,HD1205S, HD1207S, HD1210S, HD1212S, HD1215S, HD1220S, HD1225S, HD1230S, HD1235S, HD1240S, HD1250S, HDD12505S, HDD12510S, HDD12515S, HDD12520S, HDD12525S, HDD12530S, HDD12540S, HDD12550S

- Drill Stopper : DS030C, DS040C, DS050C, DS0060C, DS066C, DS070C, DS085C, DS100C, DS115C, DS130C

-IS Direction pin : DPIS35C , DPIS45C

-IS Fixture Driver : ISFD05C, ISFD05CL, ISFD10R, ISFD15R

-Drill Stopper Holder: DSHC

-Adapter/Connector : RC05, RC10, RC15, RC20, RC25, CAA00

-Parallel Pin : PP07F, PP08F, PP10F, PP11F

-Drill Extension : DE01

-Depth Gauge : DG17

-Torque Ratchet : TW60

-Driver Holder : DH02

-Profile Tap Support Holder: SGPTSH

-Driver Holder & Depth Gauge : DHDG

-Neo Surgical Kit Tray : NEOSKIT

Other Surgical Components

-Friction Driver : FD00, FH00

-Friction Driver Set : FDHSET01

-Abutment Driver : ITAD0L, ITESD00

-Bone Profile : BPN40, BPR50, BPR60, BPI60, BPI60, BPB70, BPB80, BPB90, ISBP48, ISBP55, ISBP60, ISBP68

-Thread Former : TF16,TF18,TF20,TF25

-Round Bur : RB100S, RB050S

-Abutment Positioner : AP162, AP165, AP167 ,AP202, AP205, AP207, AP252, AP255, AP257

-Abutment Positioner Driver : HDS1215, HDS1220, HDS1215S, HDS1220S

-Abutment Positioner set : AP1615, AP1620, AP2015, AP2020, AP2515, AP2520

-CTi-mem Contouring Plier : MCCC

-CTi-mem Cover Cap Driver : MCCD, CMCCD22

-Lab Analog : EBAN30, EBAR40, EBAI50, EBAB50, ITLA50, ITLA70, ITAR40, ITAR55, ITAR70, ITELA440, ITELA455, ITELA470, ITAW40, ITAW55, ITAW70, ITAS00, ITASW00, ISLA400, ISLA500, ISLA600, ISLA440, ISLA445, ISLA455, ISLA460, ISLA470, ISLA480, ISLA540, ISLA545, ISLA555, ISLA560, ISLA570, ISLA580, ISLA640, ISLA645, ISLA655,

ISLA660, ISLA670, ISLA680, ISLA740, ISLA745, ISLA755, ISLA760, ISLA770, ISLA780, ISLA445P, ISLA455P
ISLA460P, ISLA470P, ISLA480P, ISLA545P, ISLA555P, ISLA560P, ISLA570P, ISLA580P, ISLA645P, ISLA655P, ISLA660P,
ISLA670P, ISLA680P, ISLA745P, ISLA755P, ISLA760P, ISLA770P, ISLA780P, ISLA5000, MUALA48, MICLAB01, MICLAB02,
BALA350, SGISLA400, SGISLA500

-UCLA: EUPHN300, EUPHR400, EUPHI500, EUPHB500, EUPSN300, EUPSR400, EUPSI500, EUPSB500, EUPNN300,
EUPNR400, EUPNI500, EUPNB500, ITUPO500, ITUPO600, ITUPO700, ITUPN500, ITUPN600, ITUPN700, ISUPH400,
ISUPH500, ISUPH600, ISUPN400, ISUPN500, ISUPN600, MUAGCH48, MUAGCH60, MUAGCN48, MUAGCN60,
MUACCH48, MUACCH60, MUACCN48, MUACCN60, MUAPCH48, MUAPCH60, MUAPCN48, MUAPCN60, MUATPCH48,
MUATPCH60, MUATPCN48, MUATPCN60

-Coping : ITPRCR, ITHPC, ITPWCR, ITPRBR, ITNPC, ITPWBR, ISPCH410, ISPCH510, ISPCH610, ISPCH710,
ISPCN410, ISPCN510, ISPCN610, ISPCN710, MUATCH48, MUATCH60, MUATCN48, MUATCN60

-Screw (Lab) : LCSHS16, LCSHS20, LCSHS25, LITCS20S, LITAS20A, LISC20, ISCS20G, MUAS14

-Auto Chip Maker : ACM50S, ACM60S, ACM70S, ACM80S, ACM50L, ACM60L, ACM70L, ACM80L, ACM30S, ACM35S,
ACM40S, ACM45S, ACM30L, ACM35L, ACM40L, ACM45L, ACM30ESm, ACM35ES, ACM40ES, ACM45ES, ACM50ES,
ACM60ES, ACM70ES, ACM80ES

-Auto Chip Maker Stopper : ACMS50S, ACMS60S, ACMS70S, ACMS80S, ACMS50L, ACMS60L, ACMS70L, ACMS80L,
ACMS30S, ACMS35S, ACMS40S, ACMS45S, ACMS30L, ACMS35L, ACMS40L, ACMS45L, ACMSI50S, ACMSI60S,
ACMSI70S, ACMSI80S, ACMSI50L, ACMSI60L, ACMSI70L, ACMSI80L, ACMSI30S, ACMSI35S, ACMSI40S, ACMSI45S,
ACMSI30L, ACMSI35L, ACMSI40L, ACMSI45L, ACMSI30ES, ACMSI35ES, ACMSI40ES, ACMSI45ES, ACMSI50ES,
ACMSI60ES, ACMSI70ES, ACMSI80ES

-Auto Chip Maker Set : ACM50SETS, ACM60SETS, ACM70SETS, ACM80SETS, ACM50SETL, ACM60SETL,
ACM70SETL, ACM80SETL, ACM30SETS, ACM35SETS, ACM40SETS, ACM45SETS, ACM30SETL, ACM35SETL,
ACM40SETL, ACM45SETL, ACM50ISETSA, ACM60ISETSA, ACM70ISETSA, ACM80ISETSA, ACM50ISETLA,
ACM60ISETLA, ACM70ISETLA, ACM80ISETLA, ACM30ISETSA, ACM35ISETSA, ACM40ISETSA, ACM45ISETSA,
ACM30ISETLA, ACM35ISETLA, ACM40ISETLA, ACM45ISETLA, ACM50ISETS, ACM60ISETS, ACM70ISETS, ACM80ISETS,
ACM50ISETL, ACM60ISETL, ACM70ISETL, ACM80ISETL, ACM30ISETS, ACM35ISETS, ACM40ISETS, ACM45ISETS,
ACM30ISETL, ACM35ISETL, ACM40ISETL, ACM45ISETL, ACM30ISETESA, ACM35ISETESA, ACM40ISETESA,
ACM45ISETESA, ACM50ISETESA, ACM60ISETESA, ACM70ISETESA, ACM80ISETESA, ACM30ISETES, ACM35ISETES,
ACM40ISETES, ACM45ISETES, ACM50ISETES, ACM60ISETES, ACM70ISETES, ACM80ISETES, NACM30ISETES,
NACM35ISETES, NACM40ISETES, NACM45ISETES, NACM50ISETES, NACM60ISETES, NACM70ISETES, NACM80ISETES,
NACM30ISETL, NACM35ISETL, NACM40ISETL, NACM45ISETL, NACM50ISETL, NACM60ISETL, NACM70ISETL,
NACM80ISETL, NACM30ISETS, NACM35ISETS, NACM40ISETS, NACM45ISETS, NACM50ISETS, NACM60ISETS,
NACM70ISETS, NACM80ISETS

-Surgical Drill : TSD49FS

-Impression Coping : ISIPHS411P, ISIPHS511P, ISIPHS611P, ISIPH400P, ISIPH450P, ISIPH411P, ISIPH511P,
ISIPH611P, ISIPHL400P, ISIPHL450P, ISIPHL411P, ISIPHL511P, ISIPHL611P, ISIPNS411P, ISIPNS511P, ISIPNS611P,
ISIPN400P, ISIPN450P, ISIPN411P,, ISIPN511P, ISIPN611P, ISIPNL400P, ISIPNL450P, ISIPNL411P, ISIPNL511P,
ISIPNL611P, ISIPSS411P, ISIPSS511P, ISIPSS611P, ISIPS400P, ISIPS450P, ISIPS411P, ISIPS511P, ISIPS611P,
ISIPSL400P, ISIPSL450P, ISIPSL411P, ISIPSL511P, ISIPSL611P, ISIPH411O, ISIPH511O, ISIPH611O, MUAIP48,
ISITH411P, ISITH511P, ISITH611P, ISITHL411P, ISITHL511P, ISITHL611P, ISITN411P, ISITN511P
ISITN611P, ISITNL411P, ISITNL511P, ISITNL611P, ISITS411P, ISITS511P, ISITS611P, ISITSL411P, ISITSL511P,
ISITSL611P, ISITH411O, ISITH511O, ISITH611O, MUAIT48

- Impression Coping Screw : EBPISS20, EBPISS25, EBPIS16, EBPIS20, EBPIS25, EBPIS16L, EBPIS20L, EBPIS25L, EBPISL16, EBPISL20, EBPISL25, EBPISL16L, EBPISL20L, EBPISL25L, , EBTIS16, EBTIS20, EBTIS25, EBTISL16, EBTISL20, EBTISL25, EBTIS16H, EBTIS20H, EBTIS25H, EBTISL16H, EBTISL20H, EBTISL25H, ITPISS20, ITPIS20, ITPIS20L, ITPISL20, ITPISL20L, ITTIS20, ITTISL20, ITTIS20H, ITTISL20H, ISPISS20, ISPIS20, ISPIS20L ,ISPISL20, ISPISL20L, MUAIPS48, ISTIS20, ISTISL20, ISTIS20H, ISTISL20H,

-Impression Coping Set(Coping +Screw): EBIPHS411, EBIPHS511, EBIPHS611, EBIPHIS611, EBIPH411, EBIPH511, EBIPH611, EBIPHI611,, EBIPHL411, EBIPHL511, EBIPHL611, EBIPHIL611, EBIPSS411, EBIPSS511, EBIPSS611, EBIPSIS611, EBIPS411, EBIPS511, EBIPS611, EBIPSI611, EBIPSL411, EBIPSL511, EBIPSL611, EBIPSIL611, EBIPNS411, EBIPNS511, EBIPNS611, EBIPNIS611, EBIPN411, EBIPN511, EBIPN611, EBIPNI611, EBIPNL411, EBIPNL511, EBIPNL611, EBIPNIL611, EBPISS16, EBITH411, EBITH511, EBITH611, EBITHI611, EBITHL411, EBITHL511, EBITHL611, EBITHIL611, EBITS411, EBITS511, EBITS611 ,EBITSI611, EBITSL411, EBITSL511, EBITSL611, EBITSIL611, EBITN411, EBITN511, EBITN611, EBITNI611, EBITNL411, EBITNL511, EBITNL611, EBITNIL611, , ITIPOS511, ITIPOS611, ITIPO511, ITIPO611, ITIPOL511, ITIPOL611, ITIPO711, ITIPOL711, ITIPNS511, ITIPNS611, ITIPN511, ITIPN611, ITIPNL511, ITIPNL611, ITIPN711, ITIPNL711, ITITO511, ITITO611, ITITOL511, ITITOL611, ITITO711, ITITOL711, ITITN511, ITITN611

ITITNL511, ITITNL611, ITITN711, ITITNL711,ISIPHS411, ISIPHS511, ISIPHS611, ISIPH400, ISIPH450, ISIPH411, ISIPH511, ISIPH611, ISIPHL400, ISIPHL450, ISIPHL411, ISIPHL511 ,ISIPHL611, ISIPNS411, ISIPNS511, ISIPNS611, ISIPN400, ISIPN450, ISIPN411, ISIPN511, ISIPN611, ISIPNL400, ISIPNL450, ISIPNL411, ISIPNL511, ISIPNL611, ISIPSS411, ISIPSS511, ISIPSS611, ISIPS400, ISIPS450, ISIPS411, ISIPS511, ISIPS611, ISIPSL400, ISIPSL450, ISIPSL411, ISIPSL511, ISIPSL611, ISITH411, ISITH511, ISITH611, ISITHL411, ISITHL511, ISITHL611, ISITN411, ISITN511, ISITN611, ISITNL411, ISITNL511, ISITNL611, ISITS411, ISITS511, ISITS611, ISITSL411, ISITSL511, ISITSL611

-Plastic Impression Coping : ITIR00, ITEIC00, ITIW00, ITYR40, ITYR55, ITYR70, ITYW40, ITYW55, ITYW70, ITEPC40, ITEPC55, ITEPC70, ISPIC411, ISPIC511, ISPIC611, ISPIC711, MICIMP

-Protective Cap/Healing Cap : ITPR40, ITPR55, ITPR70, ITPTC40, ITPTC55, ITGCC70, ITPW40, ITPW55, ITPW70, ISPTC440, ISPTC445, ISPTC455, ISPTC470, ISPTC540, ISPTC545, ISPTC555, ISPTC570, ISPTC640, ISPTC645, ISPTC655, ISPTC670, ISPTC740, ISPTC745, ISPTC755, ISPTC770, MUAHC48, MICPTC

-Lab Cylinder Body : SGISLCBAN, SGISLCBARW

-Lab Cylinder pin : SGISLCPN, SGISLCPRW

-Lab Cylinder set(Body+Pin) : SGISLCN, SGISLCRW

-Ball Abutment Driver : BAD10, BAD15, BAD20, BADC07, BADC12

-Torx Driver : TXDC1710, TXDC1715, TXDC1720, TXD1710, TXD1715, TXD1720, TXD1710S, TXD1715S, TXD1720S

-Lindemann drill : LD20, LDS20, LDS27

-Profile Tap : PTAP35S, PTAP35L, PTAP40S, PTAP40L, PTAP45S, PTAP45L, PTAP50S, PTAP50L, PTAP35FS, PTAP40FS, PTAP45FS, PTAP50FS, PTAP55FS, PTAP35FL, PTAP40FL, PTAP45FL, PTAP50FL, PTAP55FL

-Neo Guide Twist Drill: NGTWD2207, NGTWD2208, NGTWD2210, NGTWD2211, NGTWD2213, NGTWD2214

-Neo Guide Bone Trimmer : NGBT00, NGBT15,NGBT30

-Scan body : ISSBH50NB, ISSBH50OSM, ISSBH50OS, ISSBH50DM, ISSBH50MAR, ISSBH50NANP, ISSBH50NARP, ISSBH3550AS ,ISSBH4550AS, ISSBH50ZAV4, ISSBH50ZSV3, ISSBH50ZSV4, ISSBH50ZSV5, ISSBT50DOM, ISSBT50DO, EXSBHN50, EXSBHR50, EXSBHI50, EXSBHB50, ITSBO50, ITSBO50W, ITSBO50OSR, ITSBO50OSW, ISSBT50MEZS, ISSBT50MEZR, ISSBT50NRNP, ISSBT50NRRP, ISSBT50NRWP, ISSBT60NR6P, ISSBS50STBN, ISSBS50STBR, ISSBD3050AS

-Oral Scan body : ISPSBH40NBP, ISPSBH50NBP, ISPSBH40OSMP, ISPSBH40OSP, ISPSBH50OSP, ISPSBH40DMP, ISPSBH50DMP, ISPSBS40NBP, ISPSBS50NBP, ITPSBO50P, ITPSBO50WP, ITPSBO50OSRP, ITPSBO50OSWP, ITPSBS50P, ITPSBS50WP, EXPSBHN50P, EXPSBHR50P, EXPSBHI50P, EXPSBHB50P, EXPSBSN50P, EXPSBSR50P, EXPSBSI50P, EXPSBSB50P, ISPSBH40NB, ISPSBH50NB, ISPSBH40OSM, ISPSBH40OS, ISPSBH50OS, ISPSBH40DM, ISPSBH50DM, ISPSBS40NB, ISPSBS50NB, ITPSBO50, ITPSBO50W, ITPSBO50OSR, ITPSBO50OSW, ITPSBS50, ITPSBS50W, EXPSBHN50, EXPSBHR50, EXPSBHI50, EXPSBHB50, EXPSBSN50, EXPSBSR50, EXPSBSI50, EXPSBSB50

-Scan body Screw : SBSM14, SBSM16, SBSM20, SBSM20AS, SBSM25, SBSM16OSM, SBSM18,

-Oral Scan body Screw: PSBSM16, PSBSM16OSM, PSBSM20, PSBSM25

-Slot Driver : SLOTDC 05, SLOTDC 10, SLOTDC 15, SLOTDC 20, SLOTD05, SLOTD10, SLOTD15, SLOTD20, SLOTD05S, SLOTD10S, SLOTD15S, SLOTD20S

-Multi unit Abutment Holder : MUAH48, AMUAH35

-Multi unit Abutment Driver : MUAD48 , MUAD48S

-Neo I-Brush: NISOL528, NISOL530, NISOL532, NISOL828, NISOL830, NISOL832

-Kit Tray : CSKIT, CSKITTRAY1, CSKITTRAY 2, CSKITTRAY 3, KTTB

-Two way Hex Driver : TWHD25

-Dia. Indicator Guide : DICG

-Fixture Driver : ISFD10RS, ISFD15RS

-Depth Gauge : DG17

-Hex Driver Swivel : HDSY2, HDSG2, HDSB2

-Abutment Positioner Holder : APH

-Drill Stop O-ring : ORING18285OR, ORING18285GR, ORING18285RE, ORING18285BL

-Drill Stop O-ring Set : ORING18285SET

-IS Encoded Healing Abutment Pin : ISEHAP

-Driver Holder & Depth Gauge : DHDG